SCHENCK



Integrated overhead rotary transfer machine

Fully automatic function

NC axes for all movements

Linkage with production lines

Powerful measuring unit CAB 850 based on industrial PC

Fully automatic balancing machine for electric armatures

Type 460 KBTU

Field of application

Measuring and correction of unbalance of wound armatures of various sizes and of rotors which permit milling correction. Main Application for fully automatic production lines with high production rate. Unbalance correction by milling in one or two planes.

Correction procedure

Slot milling in components
Vectorial distribution of the measured unbalance to the respective
pole heads

Profile milling

Polar unbalance correction directly in the determined angular position.

Polar slot milling

By axial adjusting of the milling spindle equipped with double slot milling cutters.

- High speed rotor transfer with overhead rotary transfer at small operating radius; shock-free transfer of the rotors due to sinusoidal movement. Grippers equipped with damage protection device.
- Correction station with digitally controlled milling and positioning device as well as with cutters touchpoint signal.
- Milling procedure can be selected without modification of control; swarf extraction from below.
- Flexible use, easy retooling and fast troubleshooting.
- Powerful measuring unit CAB 850 on the basis of an industrial PC: 15" touchscreen, digital signal processing,

software module for the calculation of various correction procedures, automatic calibration of the correction curve, large memory for data storage, operator support, retooling supported by photo sequence, diagnosis programs, statistics software, external interface.

Set-up (example of 461 KBTU)


6-station machine with fully automatic functions. Linking of stations and of the peripherals by an integrated overhead rotary transfer. Rotors can be conveyed to the machine on belt conveyors or pallets.

7 Operator panel

8 Control cabinet

9 Swarf extractor

- 1 Transfer
- 2 Measuring station
- 3 Correction station plane 1
- 4 Indexing station
- 5 Correction station plane 2



Important data at a glance			
Machine type	461 KBTU	462 KBTU	463 KBTU
Unbalance correction	Polar profile milling	Slot milling in components	Polar slot milling
Cycle time Correction in 2 planes (rotor specific)	4 s - 6 s	6 s - 8 s	4 s - 6 s
Retooling time (rotor specific)	5 - 15 min		
Achievable residual unbalance	depending on the rotor 1 - 3 gmm/kg (μm)		

SCHENCK

Balancing and Diagnostic Systems

SCHENCK RoTec GmbH Landwehrstraße 55 D-64293 Darmstadt

Tel.: +49 (0) 61 51 - 32 23 11 Fax:+49 (0) 61 51 - 32 23 15 eMail: rotec@schenck.net

Make use of our worldwide distribution network. Please see us at http://www.schenck.net/rotec